

**Gira Door Station Stainless Steel**  
High-quality, rugged door station  
for flush-mounting with stainless-  
steel front panel in single and  
multi-family houses

# GIRA

## Gira Door Station Stainless Steel

Elegant, rugged and vandal-proof



Gira Door Station Stainless Steel/4

## Gira Door Station Stainless Steel

The Gira Door Station Stainless Steel combines design and strength: It is not only beautiful with its high-quality stainless-steel front panel, it is also extremely rugged, vandal-proof and weather-resistant. The front panel and name plates match up almost seamlessly, so nothing can be inserted in the cracks.

In addition, it features name plates located behind security glass and concealed hands-free speech functions for protection of the loudspeaker and microphone. The bell buttons made of rugged stainless steel are also extremely durable.

The stainless steel door station is also available with a video function.

### Material

The ground front panel is 3 mm thick and produced from high-quality Nirosta V2A stainless steel. All variants of the door station are mounted without screws. Unlocking is carried out with a special opening tool included in the scope of supply.

### Name plates

The 5 mm thick security glass cover windows are protected against splashing water, can withstand impacts, fire or scratching and are very easy to clean. The inscription labels can be removed from the door station without disassembly. The unlocking device for this is concealed.



### Loudspeaker and microphone

The hands-free unit, like all Gira door stations, is equipped with state-of-the-art microprocessor technology, and thanks to the concealed design of the loudspeaker and microphone, it is not possible to destroy the hands-free unit with a sharp object. The advantage of this technology: The voice-controlled talk-back as well as echo and background noise suppression. The speech volume of the loud speaker is adjustable.

### Call buttons

Stainless-steel call buttons and name plates are illuminated with white LEDs. Pressing the buttons is acknowledged acoustically. This is an additional function that can be deactivated if necessary.

### Installation

The Gira Door Station Stainless Steel for flush-mounting is supplied including a built-in loud-speaker and is ready-to-connect, which saves time-consuming wiring of the call buttons. The connection of the usual Gira 2-wire bus is required for commissioning.

The station is installed in a 40 mm deep flush-mounted box (60 mm for integration of video function) with wall anchors and openings for the cable feed. Sponge rubber on the underside of the front panel seals off the station to the wall. In addition, a catch strap and the supporting surface in the flush-mounted box make installation easier.

### Connections

- 2 screw terminals for 2-wire bus
- 2 screw terminals for additional supply
- 2 system bus connector strips
- 2 sabotage contact screw terminals

### Technical data

- Power supply:  
26 V DC  $\pm$  2 V (bus voltage)
- Protection type: IP 44
- Temperature range:  
- 25 °C to 70 °C

### Gira Door Station Stainless Steel audio

Everything from single-family houses to large buildings can be equipped with the Gira door station. The product range includes a host of variants: Models for up to twelve residential units are available.



Gira Door Station  
Stainless Steel/2  
audio

Dimensions (W x H)  
160 x 218 mm



Gira Door Station  
Stainless Steel/12  
audio

Dimensions (W x H)  
270 x 285 mm

### Gira Door Station Stainless Steel video

The Gira Door Station Stainless Steel is available with a colour camera in all variants from a single-family house to a house with twelve residential units. The cover plate is made of shock-resistant plastic and is easy to replace in case of damage.



Gira Door Station  
Stainless Steel/4  
video

Dimensions (W x H)  
160 x 352 mm



Gira Door Station  
Stainless Steel/12  
video

Dimensions (W x H)  
270 x 285 mm

# GIRA

Gira  
Giersiepen GmbH & Co. KG  
Electrical installation  
systems

Industriegebiet Mermbach  
Dahlienstraße  
42477 Radevormwald

P.O. Box 1220  
42461 Radevormwald

Germany

Phone +49(0)21 95-602-0  
Fax +49(0)21 95-602-119

[www.gira.com](http://www.gira.com)  
[info@gira.com](mailto:info@gira.com)

## Dimensions (W x H)

### Audio

1-gang, 2-gang, 3-gang:  
160 x 218 mm  
4-gang, 6-gang: 160 x 285 mm  
8-gang, 9-gang: 160 x 352 mm  
10-gang, 12-gang:  
270 x 285 mm

### Video

1-gang, 2-gang: 160 x 285 mm  
3-gang, 4-gang: 160 x 352 mm  
6-gang, 8-gang, 9-gang:  
160 x 437 mm  
10-gang, 12-gang:  
270 x 285 mm

## Gira Inscription Service

Gira offers the first inscription of the call buttons free of charge on purchase of a Gira Door Station Stainless Steel. In just a few steps you can create a personal template and order via the website **[www.marking.gira.com](http://www.marking.gira.com)**. Within a few days the inscribed plastic labels are sent by post. The transparent labels are non-fading, weather-resistant, wrinkle-free and are optimally size-matched to the Gira Door Station Stainless Steel.

## Name plate dimensions (W x H)

62 x 18 mm

Subject to technical  
modifications

Additional information is  
available in the Gira catalogue  
and on the Internet at  
[www.gira.com](http://www.gira.com)