

Gira Esprit

The switch range with frame variants made of real materials glass, aluminium, brass, wenge wood and chrome. Esprit, expanded with a new colour variant: glass umber.

GIRA

Gira Esprit Real materials for the switch range New. Glass umber



Gira Esprit, 2-gang combination switch/SCHUKO socket outlet, glass umber/anthracite

New. Gira Esprit, glass umber
Over 230 functions for intelligent building technology can be installed in the Esprit switch range.



Gira Esprit

Gira Esprit is the switch range with frame variants featuring real materials. Glass, chrome, aluminium, brass or wenge wood set exciting accents for interiors, and the range is characterised by a timelessly clear-cut form oblivious to short-term design trends. Gira now supplements the glass variants black, white and mint with a new colour: glass umber. A harmonious, warm tone takes its place within the spectrum of neutral glass variants.

Large assortment

In terms of assortment depth Gira Esprit caters for every demand as well. Around 230 components for convenient, economical and secure living are available, ranging from conventional electrical installation to intelligent functions for the Gira Instabus KNX/EIB system and Gira radio bus system. All functions are available in the colours pure white, cream white glossy, aluminium and anthracite.

Gira Esprit glass

- 6 mm thick glass
- high-gloss
- lightly chamfered edges
- burr thickness: $0.3 \times 45^\circ$



Glass black/
colour aluminium



Glass white/
pure white glossy




Glass mint/
pure white glossy



New. Glass umber/
cream white glossy

Gira Esprit aluminium

- 6 mm thick aluminium E1 EV1
- matt ground and anodised
- lightly chamfered edges
- burr thickness: $0.3 \times 45^\circ$



Aluminium/
anthracite

Gira Esprit brass

- 6 mm thick brass
- high-gloss
- galvanised and gold-plated
- chamfered edges
- burr thickness: $1.5 \times 45^\circ$



Brass/
pure white glossy

Gira Esprit wenge wood

- 6 mm thick wood
- lightly chamfered edges
- burr thickness: $0.5 \times 45^\circ$



Wenge wood/
colour aluminium

Gira Esprit chrome

- 6 mm thick chrome
- high-gloss
- chamfered edges
- burr thickness: $1.5 \times 45^\circ$



Chrome/
anthracite

GIRA

Gira
Giersiepen GmbH & Co. KG
Electrical installation
systems

Industriegebiet Mermbach
Dahlienstraße
42477 Radevormwald

P.O. Box 1220
42461 Radevormwald

Germany

Tel +49 (0) 21 95 - 602 - 0
Fax +49 (0) 21 95 - 602 - 119

www.gira.com
info@gira.com

Frames

suitable for vertical and
horizontal installation

Frames in glass black, white,
mint and umber are available
as 1-gang to 5-gang variants.
All other materials are available
as 1-gang to 4-gang variants.

Dimensions (W x H)

1-gang: 95 x 95 mm
2-gang: 95 x 166 mm
3-gang: 95 x 236.8 mm
4-gang: 95 x 308 mm
5-gang: 95 x 380.2 mm

Protection type

IP 20

Design

Gira Designteam, Radevormwald

Design awards

DESIGN PLUS 2000,
Light + Building Frankfurt

red dot award 2001,
Design Zentrum NRW

Subject to technical
modifications

Further information is available
from the Gira catalogue or on
the Internet at www.gira.com