

USB power supply
2-gang

2359 00

GIRA



10865337 21/19

Safety instructions

Only operate USB power supply in protected locations, and avoid influence of humidity, dust, sun and heat.

Functional description

The 2-gang USB power supply enables batteries of mobile devices such as mobile phones and MP3 players to be charged. Up to two devices can be charged simultaneously. Please observe the charging instructions of the specific devices!



Installation



Installation and mounting of electrical devices may only be carried out by qualified electricians!

Serious injury (e.g. caused by an electric shock), fire, or material damage are possible in case of improper mounting. These instructions are part of the product and must remain with the end customer.

1. Switch off mains voltage.
2. Connect USB power supply to mains supply via the screw terminals L and N.
3. Secure device in the flush-mounted box and mount cover plate.
4. Switch on mains voltage.

Technical data

Operating voltage:	AC 120 to 240 V~, 50/60 Hz
Output voltage:	DC 5 V (±5%)
Output current:	3000 mA
Standby power:	≤ 0,1 W
Energy efficiency:	≥ 81,4%
Ambient temperature:	0 to +35 °C
Complies with:	DIN EN 60950-1/A2

Warranty

The warranty is provided in accordance with statutory requirements via the specialist trade.

Please submit or send faulty devices postage paid together with an error description to your responsible salesperson (specialist trade/installation company/electrical specialist trade).

This will forward the devices to the Gira Service Center.